

Pump Type	UPA	STR2 & SSR2						Amazon								Amazon Extra			MQ		H_Booster		CMB/CMBE	BYE-PAC	MAX-E Boost				
Bar Pressure		1.5		2.0		2.0		1.5		2.0		3.0		4.0		2.0		3.0		3.0	5.0	6.0	3.5	4.5	3.0	4.5			
Product Model	UPA 15-90 N	Twin		Single		Twin						Single		Single															
Product Model	UPA 15-90 N	STR2-1.5 C	STR2-1.5 CN	STR2-2.0 C	STR2-2.0 CN	SSR2-2.0 C	SSR2-2.0 CN	STP-1.5 B	STN-1.5 B	STP-2.0 B	STN-2.0 B	STP-3.0 B	STN-3.0 B	STP-4.0 B	STN-4.0 B	SSP-2.0 B	SSN-2.0 B	SSP-3.0 B	SSN-3.0 B	Amazon Ex CH4-30	Amazon Ex CH4-50	Amazon Ex CH4-60	MQ3-35	MQ3-45	Home Booster 3.0 bar	Home Booster 4.5 bar			
Positive / Universal Head	Positive	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Positive	Universal	Universal	Universal	Universal	Universal	Universal	Universal	Universal	Universal	Universal	Universal
Application																													
Boost hot or cold to individual taps	(X)					(X)	(X)									(X)	(X)	(X)	(X)										
Bath or Basin Mixer		(X)	(X)	(X)	(X)			(X)	(X)	(X)	(X)	(X)	(X)																
Boost Hot Water (Cold Mains & Gravity Hot)						(X)	(X)									(X)	(X)	(X)	(X)										
Shower Only (Hot & Cold Gravity)		(X)	(X)	(X)	(X)			(X)	(X)	(X)	(X)	(X)	(X)																
Multi Function Shower Head				(X)	(X)					(X)	(X)	(X)	(X)																
Standard Bath Mixer/Shower		(X)	(X)	(X)	(X)			(X)	(X)	(X)	(X)	(X)	(X)																
Shower Column (Gravity Hot & Cold)										(X)	(X)	(X)	(X)																
Bathroom Booster				(X)	(X)	(X)2	(X)2			(X)	(X)	(X)	(X)			(X)2	(X)2	(X)2	(X)2										
Electric Shower (Tank Fed)						(X)	(X)									(X)	(X)	(X)	(X)										
Boost to Combination Boiler (From Tank)																(X)		(X)			(X)								
Boost to Combination Boiler (Integrated Tank)																									(X)	(X)		(X)	
Boost to Unvented Hot Water Storage (from Tank)																		(X)	(X)	(X)	(X)	(X)	(X)	(X)				(X)	
Boost to Unvented Hot Water Storage (Integrated Tank)																									(X)	(X)		(X)	
House Booster (Gravity) - 2 Bathrooms										(X)	(X)	(X)	(X)						(X)2	(X)2									
House Booster (Gravity) - 3 Bathrooms												(X)	(X)						(X)2	(X)2	(X)2								
House Booster (Gravity) - 4 or more Bathrooms																			(X)2	(X)2	(X)2								
Commercial Booster (Cold Only)																					(X)1				(X)		(X)	(X)	
Construction Material	S/S	Composite						Brass								Cast Iron			Stainless Steel										
Pump Noise Level at 1m		55 - 65 dBA						55 - 65 dBA				< 70 dBA	55 - 65 dBA				65 dBA			65 dBA		Various		65 dBA					
Min Pipe Size (Reducer may be required)		15 mm						22 mm												1" BSPM		15 / 22mm		Various		11/4 BSPF			

* All product continuously rated / * Amazon Range WRAS approved, all other ranges WRAS compliant.

(X) = 1 pump required (X)2 = 2 pumps required