

BOOSTER FACTS AND FEATURES

	Multi-E (CRIE)	Multi-E (CME-I)	MPC-E (CRIE)
Control modes			
Constant pressure	Default	Default	Default
Constant flow	X	X	X
Constant temperature	X	X	X
Proportional pressure	-	-	X
Commissioning			
Plug'n'Pump easy start-up	X	X	-
Additional feature setup via Grundfos GO handheld remote	X	X	-
Start-up wizard via integrated LCD screen	-	-	X
Dimensions / layout			
Lowest footprint	X	-	-
Lowest booster set height	-	X	-

STANDARD IN FAST TRACK PRODUCTS:

- Dry run protection
- Soft fill feature
- Multi-master system architecture ^Δ
- Energy optimising pump cascade management
- All motors surpass IE4 benchmarks
- Stainless steel (hygienic) construction
- WRAS compliant predefined pressure tank
- Standard suction sensing plus primary & redundant discharge sensors ^Δ
- Communication upgrades possible (Grundfos CIM)


^Δ Excludes Multi-E CRIE 10-S & CME-I 10-3, which have a master-slave arrangement and no redundant discharge sensor.

be think innovate



SCAN THE QR CODE

Go directly to our Grundfos Product Center



* 5 day period applies to new orders placed before 11am for UK Mainland delivery. If the required model is already built and in stock, this can be accelerated further by choosing our premium service and ensuring shipment within 48 hours.

The WRAS Approved Product and Material Certification Marks are owned by WRAS and used with their approval.

GRUNDFOS Pumps Limited
 Grovebury Road
 Leighton Buzzard
 Beds LU7 4TL
 Tel: 01525 850000
grundfosuk@grundfos.com
www.grundfos.co.uk

GRUNDFOS

GRUNDFOS BOOSTER FAST TRACK

Introducing our new 5 day delivery and 48 hour shipment services*




The name Grundfos, the Grundfos logo, and be think innovate are registered trademarks owned by Grundfos Holding A/S or Grundfos A/S, Denmark. All rights reserved worldwide. 98693807 GB/IT-2014

be think innovate

GRUNDFOS


BOOSTER FAST TRACK RANGE

Now there is no need to compromise between Grundfos quality and fast delivery. British built with high grade materials and engineered to deliver superior efficiency with advanced control options, Grundfos is now able to offer 5 day delivery on a selected range of pressure boosting systems. PLUS, if the desired model is already in stock, ask us about our premium 48 hour service!*



PRODUCT NUMBER			
Pump type	No. of pumps	Multi-E (CRIE)	MPC-E (CRIE)
CRIE 3-4	2	98486569 (3ph)	
CRIE 3-5	2	98486615 (3ph)	
CRIE 3-8	2	98584944 (1ph)	
CRIE 3-8	3	98486672 (3ph)	98426900 (1ph)
CRIE 5-4	2	98486674 (3ph)	98426911 (1ph)
CRIE 5-4	3	98486678 (3ph)	
CRIE 5-5	2	98486722 (3ph)	98426914 (3ph)
CRIE 5-5	3	98584969 (1ph)	98426915 (3ph)
CRIE 5-9	2	98486772 (3ph)	98426917 (3ph)
CRIE 5-9	3		98426918 (3ph)
CRIE 10-3	2	98486773 (3ph)	98426933 (3ph)
CRIE 10-3	3	98486778 (3ph)	
CRIE 10-5	2	98486797 (3ph) ^A	
CRIE 10-5	3		98426939 (3ph)
CRIE 15-3	3		98426964 (3ph)

PRODUCT NUMBER		
Pump type	No. of pumps	Multi-E
CME-I 3-5	2	98486648 (3ph)
	2	98584981 (1ph)
CME-I 10-3	2	98486809 (3ph) ^A



Multi-E CRIE



MPC-E CRIE



Multi-E CME-I