

PRESSURE BOOSTER PUMPS AND SETS 2016 RANGE OVERVIEW



Grundfos have now been manufacturing pumps for over 70 years, so it is no surprise we have established ourselves as a market leader. Our insatiable appetite for innovation and development has ensured that our comprehensive range of booster pumps is one of the most advanced, efficient and reliable on the market.

Our extensive range caters for every need, from ensuring the shower in a small cottage has sufficient pressure, to supplying the world's tallest buildings with a constant and reliable water supply. We have worked hard to earn our exceptional reputation for reliability and as a result have been entrusted to equip some of the country's most iconic buildings. Our long list of high profile customers includes The Shard where water is needed 309 metres above the ground on the 72nd floor and Wimbledon which only operates at full capacity for two weeks of the year, though during these two weeks any pump failure would be catastrophic.

If pump failure is not an option, and you are looking for an efficient, environmentally friendly solution to your pumping needs, call one of our dedicated sales team on **01525 850000**.



MQ
Compact Home
Water Booster Pump

- Easy to install
- Self-priming
- Easy to operate
- Motor protection
- Dry run protection
- Low noise



Max Flow:
3.8m³/h
Max Head:
44m



CMBE
Pump with Compact
Pressure Vessel

- Variable speed
- Motor protection
- Dry run protection
- Low noise
- Plug and pump solution
- Durable stainless steel
- **WRAS approved product**



Max Flow:
7.5m³/h
Max Head:
45m



Home Booster
Self Contained Booster
System with Air Gap

- Easy installation
- Integrated 180l tank
- Dry run protection
- Plug and pump solution
- 8 litre expansion vessel
- Optional 200 litre slave tank can double storage
- Connect direct to the mains
- **WRAS approved components**



Max Flow:
2.9m³/h
Max Head:
45m




Byepac
Byelaw Compliant Pump
and Tank System

- Compact design
- Inclusive tank
- Wide range of pressures and flows available
- Dry run protection
- Low noise
- Integral controls
- Motor protection
- Suitable for CAT5 applications
- **WRAS approved components**



Max Flow:
5.7m³/h
Max Head:
50m



Max-E Boost

Large Domestic / Light Commercial Booster System

- Integral controls
- Easy to install
- Low energy consumption
- Plug-and-pump solution
- Maintains a constant discharge pressure
- Soft start and stop
- Compact installation
- Low noise
- **WRAS approved components**



Max Flow:
7.5m³/h
Max Head:
45m



Hydro GTI

Light Commercial Booster System with Integrated Tank

- Integral 60l tank reduces installation requirements
- Easy to install
- Constant pressure (variable speed only)
- Low energy consumption
- Plug-and-pump solution
- 1 or 2 pumps
- Fixed or variable speed control
- Soft fill
- Compatible with Grundfos GO remote control
- Suitable for CAT5 applications
- **WRAS approved product**



Max Flow:
7m³/h
Max Head:
105m



Hydro MULTI-E

Light / Intermediate Commercial Booster System

- Integral easy to use controls with large display
- Energy-optimised control
- 2-3 pumps in cascade
- Easy installation
- Plug and pump solution - no extra programming or cabling required
- Data communication
- Perfect constant pressure
- Reduced noise level
- Space-saving installation – no need for control cabinets
- Compatible with Grundfos GO remote control
- **WRAS approved product**



Max Flow:
78m³/h
Max Head:
105m



Hydro MPC-E

Large Commercial / Industrial Booster System

- Fully flexible control system
- Low energy consumption
- 2-6 pumps in cascade
- Easy installation
- Plug and pump solution - no extra programming or cabling required
- Large user-friendly display
- Energy-optimised control
- Data communication
- Perfect constant pressure
- Application-optimised software
- Custom built solutions available
- Reduced noise level
- Space-saving installation – no need for control cabinets
- **WRAS approved product**



Max Flow:
1080m³/h
Max Head:
155m



Max Flow:
1080m³/h
Max Head:
155m

